

SKF QuickCollect sensor

Machine monitoring made easy



SKF QuickCollect sensor

The SKF QuickCollect sensor is an easy to use bluetooth enabled handheld sensor that connects to apps on your tablet, smart phone or smart watch. Combining vibration and temperature sensing, overall data can be viewed on the spot in real time or pushed to the cloud for future analysis.

This SKF QuickCollect sensor is ideal for service, reliability, operations, or maintenance personnel as part of a walk around data collection program.

Features

- Velocity, acceleration enveloping, and temperature measurements
- Bluetooth communication with tablets, smart phones, smart watches
- Easy to use sensor and apps
- Easy to understand indications of machine condition
- Rugged industrial design Drop test 1,8 m (6 ft.), water and dust resistant (IP65)
- Suitable for use in hazardous environments (ATEX Zone 1, Class 1, Div 1)
- Rechargeable lithium battery (8 hours normal usage)
- Option to connect, store and share data on the Cloud
- Option to connect directly to SKF Remote Diagnostic Services

Benefits

- Gets you started quickly
- Can be used with minimum training and experience
- Identify developing rotating machinery issues before they become problems
- Connect directly to expert advice when you need it
- Expand functionality via apps to grow and compliment your existing maintenance program

Controls and indicators




2 **5KF**.

Measurement displays

Measurements taken by the sensor are shown on your mobile device, which displays velocity, acceleration, and temperature as shown below:


Each reading displays a current overall measurement, including alarm status, minimum and maximum values, and alert and danger thresholds.



SKF Enlight QuickCollect System

The SKF QuickCollect sensor can be used with the SKF QuickCollect app, or with SKF DataCollect app which provides additional functionality, including the ability to store

and share data via the SKF cloud, and to directly access SKF Remote Diagnostic Services.



Technical specifications

Environmental and regulatory specifications

Non-hazardous areas: -20 to +60 °C Temperature range

Hazardous areas: -20 to +60 °C Charging: 0 to +40 °C

95% non-condensing

IP rating IP 65, Dust and water ingress protection testing standard.

Class 1 Division 1 Group A, B, C, D certification Hazardous approval

(North America) Class 1 Zone 1 (pending)

ATEX Zone 1 certification (pending) Hazardous approval (Europe)

Area = II (non-mining) Category = 2G (Zone 1) Ex ib IICT4

Europe (CE), USA (FCC), Canada (IC) Radio Approvals

CE Mark CE approved

Measurement range

Overalls

Humidity

10 Hz to 1 kHz up to 55 mm/s Velocity:

Bearing condition: SKF patented Envelope acceleration up to 20~gE

Maximum Frequency: Velocity 1 kHz, Enveloped Acceleration 2 kHz Lines of resolution: Velocity 400, Enveloped acceleration 800

Detection type: Velocity RMS, Enveloped acceleration True Peak to Peak

Power

Charger

Rechargeable lithium battery, 3,7 V DC. 0,14 A Main Power

Battery Lifetime Eight hours with normal usage

MAINS supply voltage, charger Varies up to ±10% of the nominal voltage

TRANSIENT OVERVOLTAGE CATEGORY II; POLLUTION DEGREE 2

Input 5 V DC ± 10%, 1 A

AC Adapter Input 100 to 240 V DC, 0,4 A, 47 to 63 Hz Output 5 V DC, 1,6 A

Environmental

-20 to +45 °C (–5 to +115 °F) for less than one month -20 to +35 °C (–5 to +95 °F) for less than six months 0 to +40 °C (32 to +105 °F) for charging Storage Temperature

Operating Temperature, Battery

 $-20 \text{ to} + 60 ^{\circ}\text{C} (-5 \text{ to} + 140 ^{\circ}\text{F})$ for discharging 0 to $+40 ^{\circ}\text{C} (32 \text{ to} + 105 ^{\circ}\text{F})$

Operating Temperature, Charger Up to 2000 m (6 560 ft.) Altitude

Humidity 95% non-condensing

Physical

Water and dust resistant (IP65) Case Drop test 1,8 m (6 ft.) to concrete

Dimensions 45 x 45 x 135 mm (1.8 x 1.8 x 5.3 in.)

Weight 200 g (7 oz.)

skf.com | skf.com/cm

® SKF is a registered trademark of the SKF Group.

© SKF Group 2017

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB CM/P2 17198 EN · May 2017